
# INKER & RASOR



### MODEL APS Holiday Detector 800v to 35,000v

Info@tinker-rasor.com

O BATTERY RELEASE BELOW

INKER&RASO

#### DESIGNED WITH SAFETY IN MIND!

SAFETY FEATURE DIGITAL VOLTAGE DISPLAY LED HOLIDAY INDICATOR ERGONOMIC DESIGN VOLUME CONTROL

Distributed by

MESA PRODUCTS INC. 4445 S. 74th E. Ave. Tulsa, OK 74145 Phone: 918-627-3188

1-888-800-MESA

www.teststations.com

## www.tinker-rasor.com

Info@tinker-rasor.com

www.detectron.com

Instrument will work only when safety handle is depressed.

SAFETY

HANDLE



Tinker & Rasor quality is found in our products, our people and our customer service.





### PRODUCT DATA SHEET MODEL APS HOLIDAY DETECTOR

#### Features:

- SAFETY SWITCH INSTANT SHUT OFF
- In Operation indicators
- 800v 35000v in one instrument • Volume adjustment for use in
- loud environments
- Super Bright visual holiday indicator
- Ergonomic handle and grip
- Low battery voltage indicator
- Regulated voltage
- Push button operation
- Compatible with Models AP/S1 & AP/S2 accessories (wand, battery, ground cable)

#### **Construction:**

- Rugged design for long life
- Water & Dust Resistant Carrying Case
- Weather sealed
- Solid state electronics

#### **Applications:**

- · Pipelines and other coated structures
- Wide variety of coatings materials
- Thin to thick coatings

#### **Specifications:**

- Pulsating DC output voltage
- Low: 800v to 8,000v
- High: 3,500v to 35,000v
- 100v Resolution (Meter)
- +/- 5% Accuracy
- Battery operated (6v)
- 110v AC Charger (220v available)

#### **Dimensions:**

- 2.5" x 21.5" x 2.75" Instrument only
- 5" x 2.5" x 5.5" Battery box

#### **Carrying Case:**

40.5" x 17" x 7" (1028.7 x 431.8 x 177.8 mm) 40 lbs. (18.14kg) Shipping Weight\* \*Weight will vary based upon electrode choices

DELIVERY: Immediately from STOCK EX-Works San Bernardino, CA USA SERVICE: 24-hour Turn-Around TERMS: Net30 Days, on approval of credit WARRANTY: 3 Years, parts and labor



Kit Includes: Instrument (2) Batteries, w/ Case Ground Cable Wand Handle Inspection Paddle Carrying Case Instruction Manual Letter of Calibration

Electrode (Choose One): Full Circle Spring Electrode for any one pipe diameter between 2" and 36"

Half Circle Spring Electrode for any one pipe, 0.75" and 8"

Silicone-Rubber Brush Electrode with any one width between 2" and 8"

#### MODEL APS HOLIDAY DETECTOR